



## Anatomy of a Vitrified Dressing Tool


Utilizing the latest porous ceramic bonding technology

### Advantages

- Porous structure:
  - Maximum diamond exposure
  - Less bond/wheel interaction
  - Cooler cutting
  - Self sharpening
- Lowest possible dressing forces
- Does not dull the grinding wheel
- No wheel break-in needed after dress
- Sharper / more efficient grinding
- Higher skip dress possible
- Improved workpiece quality
- Longer wheel life
- Properties can be customized



Porous Diamond Encrusted Matrix



Optional CVD inserts for Edge or Profile Reinforcement

